# **RILEY**

# **QUADRO**™

Quadro™ offers high level comfort and wide angle vision in a versatile frame. The side arms can easily be removed and replaced with the head strap to provide an enhanced fit in challenging conditions.













INNER SEAL

SOFT TPE

TempFLEX™



Quadro™ available with adjustable head strap

## **KEY FEATURES**

- + Sports style design
- + Single piece panoramic lens
- + Soft comfort TPE inserts on temple ends
- → Washable, soft TPE/foam inner frame seal provides a close, comfortable facial fit
- + Side-arms can be removed and easily replaced by the enclosed head strap
- + Supplied with a microfibre storage pouch
- → Meets high impact B rating when worn with headstrap

LENS		REF.	LENS MARKING	FRAME MARKING	PROTECTION AGAINST	COATINGS
CLEAR	R ()	RLY00311	2C -1.2 <b>₹</b> 1FTKN <b>(€</b> / Z87+ U6	スF: EN 166 FT <b>は (€</b> /Z87+ スB: EN 166 BT <b>は (€</b> /Z87+	Impacts, UV radiations	TECTON HOD  K&N Anti-scratch +
GREY		RLY00312	5-2.5 <b>₹</b> 1FTKN <b>(€</b> /Z87+U6 L2.5	ス F: EN 166 FT <b>は (€</b> /Z87+ ス B: EN 166 BT <b>は (€</b> /Z87+	Impacts, UV and Solar radiations	Anti-fog / UV400 / Moisture repellent



# QUADRO

### **GENERAL SPECIFICATION**

LENS BASE	8mm	
WEIGHT	31g	

### **PACKAGING**

Individually contained in a polythene bag with a Euroslot

PER BOX	10
PER CARTON	200

### COMPONENT SPECIFICATION

COMPONENT	MATERIAL	FEATURES	
LENS	Polycarbonate	Single piece panoramic lens	
NOSE BRIDGE	Thermoplastic Elastomers (TPE)	Comfortable and flexible	
TEMPLE	Nylon/Thermoplastic Elastomers (TPE)	Co-injected - Soft and comfortable	
HINGE	Nylon	Durable	

### LENS & FRAME MARKINGS

### **LENS MARKINGS**

### I FNS FILTER TYPE:

2, 2C UV | 4 IR filter | 5, 6 Solar filter | 1.7 to 7 Welding filter if no shade

### SCALE NUMBER (SHADE):

1.2 Clear or Amber
1.4 Blue or I/O Waterproof
1.7 Minimises or I/O
2.5 Grey or Revo
3.1 Dark Grey or Mirror

☐ Identity of manufacturer

### OPTICAL CLASS:

1 High optical quality

### MECHANICAL STRENGTH:

Increased strength

Low energy impact, resists a 6mm, 0.86g ball at 45m/s

Medium energy impact, resists a 6mm, 0.86g ball at 120m/s

High energy impact, resists a 6mm, 0.86g ball at 190m/s

Protection against high-speed particles at extreme temperatures

### PERFORMANCE:

Short circuit electric arc

Molten metal splash

Resistance to scratches by fine particles

N Resistance to fogging

Certification mark

## FRAME MARKINGS

### Identity of manufacturer

EN 166: guaranteed minimum resistance of the protective eyewear against everyday risks including dropping the protective eyewear onto the ground, ageing by light exposure, exposure to heat or corrosion etc.

### MECHANICAL STRENGTH:

S Increased strength

Low energy impact, resists a 6mm, 0.86 g ball at 45m/s

Medium energy impact, resists a 6mm, 0.86 ball at 120m/s

High energy impact, resists a 6mm, 0.86 ball at 190m/s

Protection against high-speed particles at extreme temperatures

### PERFORMANCE

Liquid droplets or splashes

Large dust particles > 5 µm

Gases and small dust particles < 5 µm

Short circuit electric arc Molten metal and hot solids

UK ( Certification marks

#### USA (ANSI)

LENS:

UV (All lenses) L1.3 LED L2.5 Solar (Grey) L3 Solar (Dark Grey)

L1.7 Solar (I/O, Twilight) W4 Infrared lens

Standard Mark

(SAI Global)

LENS AND FRAME:

Z87+ High velocity impact, 0.25 inch, 1.04g ball at 150ft/s

### AUS (AS/NZS)

### LENS MARKINGS:

## OCULAR CATEGORY:

0 UV 1 Solar 2 Solar 3 Solar O Outdoor untinted

### MECHANICAL STRENGTH:

I Medium energy impact, resists a 6mm, 0.86g ball at 45m/s

### FRAME MARKINGS:

AS/NZS 1337.1: 2010 guaranteed minimum resistance of the protective eyewear against everyday risks including dropping the protective eyewear onto the ground, ageing by light exposure, exposure to heat or corrosion etc.

### **CLEANING AND STORAGE**

CLEANING: The lenses should be cleaned regularly.

MAINTENANCE: Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfibre pouch or rigid case.

STORAGE: All products must be stored in a dry and clean environment.

Riley product approval certificates to CE standards will be provided on request. Riley is a registered trademark.

### CERTIFICATION

Product conforms to the requirement of: UK Regulation 2016/425 on PPE, brought into UK Law and amended & Regulation (EU) 2016/425 of the European Parliament and of the Council as Personal Protective Equipment (PPE).

Type-Examination, (Module B), Certificates issued by: UK - INSPEC International Ltd. 56 Leslie Hough Way, Salford, Greater Manchester M6 6AJ UK [A.B. No. 0194]. EU - INSPEC International B.V. Beechavenue 54, 1119 PW, Schiphol-Rijk, Netherlands [N.B. No. 2849]

Authorised Representative [EU]: Globus EMEA Ltd., 51 Dawson Street, Dublin, D02 AN25, Ireland.

### www.riley-eyewear.com

**E:** info@riley-eyewear.com

T: +44 (0)161 877 4747

F: +44 (0)161 877 4746

Globus (Shetland) Ltd, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UK

